

Corning Ribbon Ceramics Platform

Leveraging its unparalleled expertise in ceramic science, Corning has invented a new way to manufacture high performance, fully dense ceramic ribbon in roll-to-roll (R2R) format, which is a revolution in the processing of ceramic materials. This new manufacturing process enables us to make high performance wafers, panels, and long length ribbons with unique form factors for hydrogen production, sensors, and other applications.

Zirconia Ribbon Ceramic

Properties

- Thin, flexible, and available in multiple sizes
- Smooth surface, clean edges, and supporting small vias formation
- Thermal shock resistance with no outgassing
- Lightweight and wear resistant
- Corrosion resistant


Physical Properties

Physical	
Material	3YSZ
Surface Roughness (R_a)	~20/50 nm
Grain Size	0.45 μm
Porosity	< 0.5%
Outgassing	0%
Mechanical	
Bend Strength	1 GPa
Bulk Strength (BoCR)	1.8 GPa
Thermal	
Operating Temperature	$\leq 1,000^\circ \text{C}$
Thermal Conductivity	~2.7 W/mK
Electrical	
DC Dielectric Strength (kV/mm) (40 μm)	200
Dielectric Constant (Dk) (2.6 GHz)	~28

**Properties of this table are measured from developmental samples and are expected but not guaranteed.*

Unique Form Factor | Roll to Roll

For the first time, zirconia ceramic substrates are available as thin as 20 μm at widths up to 200mm and meter scale lengths. This unique form factor allows the ribbon to flex and be laminated to curved surfaces. In addition, post processing of long length formats enables faster production and new application technologies.




Potential Applications

- Ionic conducting processes including hydrogen (H_2) production (SOEC & SOFC)
- Thin film solid state battery substrate
- Hybrid flexible electronic sensors
- Harsh environment sensor

Roll to Roll (R2R) Metalization

Zirconia Ribbon Ceramic can be metallized on a variety of roll-to-roll process such as vacuum sputtering, screen printing, slot die coating, or electrode plating. The image below shows a section of zirconia ribbon ceramic sputter coated with copper from a roll-to-roll process.



Availability

Available at thicknesses of 20 μm and 40 μm in the following sample sizes:


- 4" wafers
- Custom dimensions

Ribbon format for R2R processing may be discussed on a project basis.




Ionic Properties

Zirconia Ribbon Ceramic exhibits high ionic conductivity at elevated temperature.



Durable, Flexible, and Robust

Zirconia Ribbon Ceramic is thin, flexible, and mechanically durable with a smooth, low-defect surface.



Contact Us

Email: RBNCERAMIC@corning.com

Corning reserves the right to change its product specifications at any time without notice. Please ensure you have the latest applicable specification before purchasing a Corning product. It is customer responsibility to determine the suitability of Corning's product to its own application. Corning does not provide any warranty of merchantability or fitness for a particular purpose. Product specifications are available upon request at RBNCERAMIC@corning.com.